

Transparent Holographic Components (THCs) enable bright, transparent, virtual images to be viewed in products such as augmented-reality glasses, smart glasses, head-up displays, vehicular displays, and near-to-eye displays. Luminit THCs use highly efficient holographic optical elements that direct light beams without the need for bulky and expensive optics. Luminit holographic technologies for near-to-eye or head-up displays use thin (10-30 micron) holographic photopolymer film. The holograms recorded in this film have properties of thick (Bragg) holograms that are wavelength and angle selective, with very low scattering. Their unparalleled transparency (>90%) and diffraction efficiency (>90% at peak) mean that THCs deliver brighter, more compact designs with larger virtual image size for head-up and head-mounted displays.

## **B**ENEFITS

- More efficient product design
- LARGER VIRTUAL IMAGE SIZE
- REDUCED WEIGHT AND MORE FLEXIBILITY IN PACKAGING DESIGN
- REDUCTIONS IN POWER CONSUMPTION DUE TO INCREASED EFFICIENCY

## **SPECIFICATIONS:**

MATERIAL COMPOSITION: POLYMER THIN FILM ON GLASS OR

**PLASTIC** 

MINIMUM SIZE: < 1 CM<sup>2</sup>
MAXIMUM SIZE: > 1 FT<sup>2</sup>

THICKNESSES: 10-30UM FILM ON VARIOUS SUBSTRATES

**BRIGHTNESS UNIFORMITY: > 80%** 

SUBSTRATE: GLASS, ACRYLIC, POLYCARBONATE

**DIFFRACTION EFFICIENCY: UP TO 90%** 

**TRANSMISSION RATE: > 90%** 

## **APPLICATIONS**

- AUGMENTED REALITY & VIRTUAL REALITY
- AUTOMOTIVE HEAD UP DISPLAYS ON WINDSHIELDS
- HEAD-MOUNTED DISPLAYS FOR OFF-AXIS IMAGE PROJECTION
- Personal wearable display eyewear
- EYE-TRACKING
- More efficient backlighting on LED and LCD lighting
- ENHANCED SOLAR CONCENTRATORS, OPTICAL SENSORS AND SPECTROMETERS
- INCREASED HIGH CAPACITY RECORDING MEMORY
- AUTOMOTIVE INTERIOR LIGHTING SUCH AS DOME AND FLOOR LIGHTS
- WELCOME LIGHTING OR MUD LIGHTS